



Chameleon Ultra Family








Widely Tunable, Hands-Free, Modelocked Ti:Sapphire Lasers

Features

- Hands-free operation
- Sealed maintenance-free design
- Ultrawide tuning range (up to 400 nm)
- High output power (up to >3.3W)
- Pulse width optimized for minimal broadening in MPE microscope systems
- Ready for Chameleon PreComp module for negative dispersion
- Ready for Chameleon OPO wavelength extension up to 1580 nm
- Tuning above 920 nm provided by MRU air recirculator (included)
- Simple menu-driven GUI or RS-232 operator interface
- PowerTrack™ active alignment for long-term stability
- On-board spectrometer with simple USB interface shows wavelength



Mechanical Specifications



Superior Reliability & Performance

Chameleon™ Ultra Family

Widely Tunable, Hands-Free, Modelocked Ti:Sapphire Lasers

System Specifications

	Chameleon Ultra	Chameleon Ultra I	Chameleon Ultra II
Peak Power ¹ (W)	>2.5	>2.9	>3.3
Tuning Range (nm)	690 to 1020	690 to 1040	680 to 1080
Power Specifications	500 mW @ 690 nm 1.4W @ 710 nm 2.5W @ 800 nm 1.4W @ 920 nm 450 mW @ 1020 nm	600 mW @ 690 nm 1.5W @ 710 nm 2.9W @ 800 nm 1.45W @ 920 nm 450 mW @ 1020 nm 300 mW @ 1040 nm	600 mW @ 680 nm 1.5W @ 700 nm 3.3W @ 800 nm 1.5W @ 920 nm 500 mW @ 1020 nm 200 mW @ 1080 nm
Tuning Speed ² (nm/s)	>35	>40	>40
Pulse Width ^{1,3} (fs)		140	
Noise ⁴ (%)		<0.15	
Output Power Stability ⁵ (%)		<±0.5	
Spatial Mode		TEM ₀₀ (M ² <1.1)	
Beam Diameter ^{1,6} (mm)		1.2 ±0.2	
Beam Ellipticity ^{1,7}		0.9 to 1.1	
Astigmatism		<10%	
Repetition Rate (MHz)		80	
Polarization		Horizontal	
Pointing (μrad/nm)		>500:1	
		<0.5	

Utility and Environmental Requirements

Operating Voltage	90 to 250 VAC (auto ranging)
Maximum Operating Current	<15A at 90 VAC (power supply) <7A at 90 VAC (chiller) <2A at 90 VAC (MRU X1)
System Power Consumption	2300W max., 1300W typical
Line Frequency	47 to 63 Hz
Operating Temperature Range	15 to 35°C (59 to 95°F)
Weight of Laser Head	42 kg (93 lbs.)
Weight of Power Supply	41 kg (90 lbs.)
Umbilical Length	4 m (13 ft.)
Chiller:	
Dimensions (L x W x H)	27 x 20 x 38 cm (11 x 8 x 15 in.)
Weight	11 kg (25 lbs.)
MRU Air Recirculator:	
Dimensions (L x W x H)	46 x 43 x 8.5 cm (18 x 17 x 3 in.)
Weight	9 kg (20 lbs.)

¹ Specified at peak of tuning range.

² Average speed measured over entire tuning range.

³ Based on sech² deconvolution of 0.65 times autocorrelation width.


⁴ Measured RMS in a 10 Hz to 20 MHz bandwidth.

⁵ Power drift in any two-hour period with less than ±1°C temperature change after a one-hour warm-up.

⁶ 1/e² at exit port.

⁷ Ratio of major to minor 1/e² beam diameter at exit port.

Chameleon-Ultra II Typical Tuning Curve



Coherent follows a policy of continuous product improvement. Specifications are subject to change without notice.

Coherent's scientific and industrial lasers are certified to comply with the Federal Regulations (21 CFR Subchapter J) as administered by the Center for Devices and Radiological Health on all systems ordered for shipment after August 2, 1976.

Coherent offers a limited warranty for all Chameleon systems. For full details of this warranty coverage, please refer to the Service section at www.Coherent.com or contact your local Sales or Service Representative.



www.Coherent.com

Coherent, Inc.
5100 Patrick Henry Drive
Santa Clara, CA 95054
phone (800) 527-3786
(408) 764-4983
fax (800) 362-1170
(408) 988-6838
e-mail tech.sales@Coherent.com

Benelux +31 (30) 280 6060
China +86 (10) 6280 0209
France +33 (0)1 6985 5145
Germany +49 (6071) 9680
Italy +39 (02) 34 530 214
Japan +81 (3) 5635 8700
Korea +82 (2) 460 7900
UK +44 (1353) 658 833

